

Garant**VNMG 160404, Grade: HB7020**

Order data

Order number	251732 HB7020
GTIN	4045197717092
Item class	21G

Technical description

Cutting depth a_p	0.3 - 2 mm
Cutting conditions	slightly interrupted
Chip breaker	SS
Main application	P
Corner radius	0.4 mm
Cutting speed v_c main application	150 - 400 m/min
Feed f	0.08 - 0.4 mm/rev.
Grade	HB7020
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	VNMG 160404

Number of changes/inserts	4
Type of product	Indexable insert for turning