

**Plug-in adapter reducer, Type: 2****Order data**

Order number	657949 2
GTIN	4018754161041
Item class	63A

**Description****Version:**

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

**Material:**

Chrome alloy steel, non-flaking, chrome-plated over nickel.

**Cutting dataa:****Legend for drawing and formula:**

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

$L$  = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

**Suitable for:**

Torque wrench with rectangular sockets.

**Note:**

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

## Technical description

Width b	28 mm
Plug-in shank	14×18 mm
for plug-in heads	9×12 mm
Height h	21 mm
Series	7370/40
Pitch S	21.5 mm
Exchangeable tool	Plug-in head
Type of product	Screwdriver set