


Garant
SNMG 120412, Grade: HB725


Order data

Order number	251226 HB725
GTIN	4045197713407
Item class	21G

Description

SNMG 120412 HB725 Corner radius: 1.2 mm
 Grade: HB725
 Chip breaker: UM
 Cutting depth a_p : 0.5 - 5 mm
 Feed f : 0.2 - 0.6 mm/rev.
 Cutting speed v_c main application: 50 - 250 m/min

Technical description

Chip breaker	UM
Corner radius	1.2 mm
Main application	UNI
Cutting depth a_p	0.5 - 5 mm
Feed f	0.2 - 0.6 mm/rev.
Cutting conditions	slightly interrupted
Grade	HB725

Cutting speed v_c main application	50 - 250 m/min
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	SNMG 120412
Number of changes/inserts	8
Type of product	Indexable insert for turning