


Garant**Indexable insert for turning WNMG 080412, for medium machining****Order data**

Order number	252072 HB725
GTIN	4045197713506
Item class	21G

Technical description

Corner radius	1.2 mm
Cutting speed v_c main application	50 - 250 m/min
Feed f	0.2 - 0.6 mm/rev.
Cutting depth a_p	0.5 - 5 mm
Cutting conditions	slightly interrupted
Chip breaker	UM
Main application	UNI
Type	HB725
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	WNMG 080412
Number of changes/inserts	6

Data sheet

Tolerance	M
Type of product	Indexable insert for turning