

Garant**TN.G 160404, Grade: HB725**

Order data

Order number	251542 HB725
GTIN	4045197713414
Item class	21G

Description

TN.G 160404 HB725 Grade: HB725

Chip breaker: UM

Tolerance: M

Cutting depth a_p : 0.5 - 5 mmFeed f : 0.2 - 0.6 mm/rev.Cutting speed v_c main application: 50 - 250 m/min

Technical description

Feed f	0.2 - 0.6 mm/rev.
Main application	UNI
Cutting speed v_c main application	50 - 250 m/min
Chip breaker	UM
Cutting depth a_p	0.5 - 5 mm
Corner radius	0.4 mm
Cutting conditions	slightly interrupted

Grade	HB725
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	TN.G 160404
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning