



Base body MT shank, without through-coolant, 1.5xD, Type: 36



Order data

Order number	232257 36
GTIN	4045197717887
Item class	22G

Description

Version:

For holes up to IT10 accuracy.

Straight fluted.

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Through-coolant: no

Number of cutting edges Z: 2

Dia. range D_c : 36 - 47 mm

Reach L_1 : 70.5 mm

Morse taper MT size: 4

Clamping screws: 232990 TX20

Technical description

Dia. range D_c	36 - 47 mm
Clamping screws	232990 TX20
Reach L_1	70.5 mm
Morse taper MT size	4
Number of cutting edges Z	2
Version	1.5xD
Shank	Morse taper
Through-coolant	no

Type of product	Indexable drill
-----------------	-----------------

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Torx® set of screws 10 pieces Drive TX20	232990 TX20
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600