

SWISS TOOLS

Cutting head, right-hand, Shank Ø / insert size: 40/11 mm



Order data

Order number	260316 40/11
GTIN	2050001912312
Item class	29D

Description

Version:

Interchangeable cutting heads for HSK-T and PSC base bodies. Optimum cooling via aligned High Pressure Cooling nozzles.

Suitable for :

Boring bar base body **No. 320102; 320103; 320407; 320408.**

Through-coolant: yes

Cutting point / joint: 40 mm

ISO code indexable cutting head: SDUCR/L

suitable indexable insert: DC.. 11T3..

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre-line offset: 27 mm

Overall length: 40 mm

Technical description

Minimum pre-drill $\varnothing D_{\min}$	50 mm
suitable indexable insert	DC.. 11T3..
Cutting point / joint	40 mm

Insert size	11 mm
Centre-line offset	27 mm
ISO code indexable cutting head	SDUCR/L
Insert screw	320624_2
Shank Ø	40 mm
Overall length	40 mm
Insert assignment	left-hand and neutral
Series	Cutting head
Application type	right-hand
Through-coolant	yes

Accessories

Torx-screw No. 2 Type 2	320624 2
-------------------------	----------