


**Garant****SNMG 120408, Grade: HB725**

## Order data

Order number	251224 HB725
GTIN	4045197713391
Item class	21G

## Description

SNMG 120408 HB725 Corner radius: 0.8 mm  
Grade: HB725  
Chip breaker: UM  
Cutting depth  $a_p$ : 0.5 - 5 mm  
Feed  $f$ : 0.2 - 0.6 mm/rev.  
Cutting speed  $v_c$  main application: 50 - 250 m/min

## Technical description

Cutting depth $a_p$	0.5 - 5 mm
Feed $f$	0.2 - 0.6 mm/rev.
Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Chip breaker	UM
Main application	UNI
Grade	HB725

Cutting speed $v_c$ main application	50 - 250 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Type of product	Indexable insert for turning