

Garant
GARANT Master Tap INOX machine tap HSS-E-PM Form C 6HX, TiAlN, M: M2,6

Order data

Order number	135732 M2,6
GTIN	4062406075279
Item class	111

Description
Version:

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials**.

The 45° helix angle of the flutes facilitates chip formation especially in ductile austenitic CrNi steels.

- **HSS-E-PM tool material for a high degree of wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2X 6HX

Thread pitch: 0.45 mm

Overall length L: 50 mm

Shank $\varnothing D_s$: 2.8 mm

Shank square \square : 2.1 mm

Tapping hole \varnothing : 2.1 mm

Technical description

Thread type	M
Tool material	HSS E PM
Overall length L	50 mm
Number of clamping slots	3
Shank square \square	2.1 mm

Thread depth	6.5 mm
Standard	DIN 371
Thread pitch	0.45 mm
Thread Ø	2.6 mm
Tapping hole Ø	2.1 mm
Tolerance class	ISO 2X 6HX
Number of cutting edges Z	3
Shank Ø D _s	2.8 mm
Thread size	M2.6
Coating	TiAlN
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	C
Helix angle	45 °
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P

Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		