

Garant
GARANT Master Tap INOX machine tap HSS-E-PM Form C 6HX, TiAlN, M: M6

Order data

Order number	135732 M6
GTIN	4062406081416
Item class	111

Description
Version:

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials**.

The 45° helix angle of the flutes facilitates chip formation especially in ductile austenitic CrNi steels.

- **HSS-E-PM tool material for a high degree of wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2X 6HX

Thread pitch: 1 mm

Overall length L: 80 mm

Shank $\varnothing D_s$: 6 mm

Shank square \square : 4.9 mm

Tapping hole \varnothing : 5 mm

Technical description

Thread pitch	1 mm
Thread depth	15 mm
Overall length L	80 mm
Tapping hole \varnothing	5 mm
Shank $\varnothing D_s$	6 mm

Standard	DIN 371
Number of cutting edges Z	3
Thread type	M
Thread Ø	6 mm
Shank square □	4.9 mm
Number of clamping slots	3
Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Thread size	M6
Coating	TiAlN
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	C
Helix angle	45 °
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P

Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		