

Garant

**Plunge milling cutter 90°, with threaded shank, Ø D / number of teeth Z:
32/4mm**


Order data

Order number	211851 32/4
GTIN	4045197715111
Item class	210

Description
Version:

Greater tool stiffness by elimination of twist between indexable insert and insert seat.
Can be extended as required using the threaded connection.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 0.9** with bit No. **674252 size 7IP**.

Technical description

Ø D ₁ h6	17 mm
Ø D ₂	28.7 mm
Pack of insert screws	219801 (7IP; 0.9 Nm)
Cutting edge Ø D _c	32 mm
Mounting thread M	M16
suitable indexable insert	VDGT 11T2..
Overall length L _{tot}	42 mm
Number of cutting edges Z	4
Ramping length L for α _{max}	28.4 mm

Circular interpolation milling $\varnothing D_{\max}$	62 mm
Circular interpolation milling a_p	3.5 mm
Ramping angle α_{\max}	3.02 degrees
Circular interpolation milling $\varnothing D_{\min}$	62 mm
$\varnothing D_3$	30 mm
Shank type	with threaded shank
Setting angle κ	90 degrees
Milling application	Circular milling
Milling application	Ramping
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	Plunge mill

Accessories

Set of insert screws 10-piece	219801
Torque screwdriver, fixed setting set torque 0,9 N·m	211750 0,9
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 7IP	674252 7IP