

3M**Mini-linishing belt Ø 90×100 mm, 947A, Grit: 40****Order data**

Order number	568526 40
GTIN	4054596059245
Item class	53S

Description**Version:**

Mini-belts Ø 90×100 mm (289×100 mm).

Premium linishing belt with precisely formed **Cubitron™ II** ceramic grit (self-sharpening). With grinding aids for even cooler grinding.

Application:

For use on surface grinding and burnishing machines with backing rollers No. 568570 / 568575 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

Clear step forward in performance on **materials that are difficult to machine** such as stainless steel, nickel alloys, chrome alloys and aluminium.

Grinding medium code: Ceramic

Iron, sulphur and chlorine constituents: < 0.1 %

Technical description

Linishing belt width	100 mm
Linishing belt Ø	90 mm
Grit	40
Grinding medium code	Ceramic

Iron, sulphur and chlorine constituents	< 0.1 %
Manufacturer's designation	947A

Accessories

Backing roller Ø 90×100 mm Type AIR	568580 AIR
Backing roller Ø 90×100 mm Type SOFT	568580 SOFT
Backing roller Ø 90×100 mm Type HARD	568580 HARD