


Garant**SOGX 050204, HB6535, Type: UNI****Order data**

Order number	234032 UNI
GTIN	4062406082987
Item class	21E

Description**Suitable for:**

GARANT Power Drill No. 234000 – 234025.

Recommendation:

When spot drilling with holder No. 234015 and No. 234025, reduce the feed rate to 70%.

Feed f: 0.05 - 0.1 mm/rev.

Technical description

Series	Power Drill
Type	UNI
Number of changes/inserts	4
Coating	TiN
ISO code indexable insert	SOGX 050204
Grade	HB6535
Tool material	Carbide

Feed f	0.05 - 0.1 mm/rev.
Type of product	Indexable insert for drilling

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	270 m/min	P
Steel < 750 N/mm ²	suitable	250 m/min	P
Steel < 900 N/mm ²	suitable	220 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	180 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	170 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	150 m/min	M
CuZn	suitable only under restricted conditions	250 m/min	N
wet maximum	suitable		