

Garant GRIDLINE**Workbench with undercarriage, height 950 mm with Eluplan worktop, dark, 20×20G, Worktop length: 1500mm****Order data**

Order number	923677 1500
GTIN	4062406086121
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section, **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered using the 2-component Haptoprene® lifting handle. This combines high stability at the point of use with the ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Drawer casing 24G can be locked centrally with cylinder lock.

**Fitted with:**

Drawer front height each side mm: 75

Door height each side mm: 525

Number of height-adjustable storage shelves: 2

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Drawer usable area in G	20×20
-------------------------	-------

Drawer usable depth	500 mm
Drawer body usable height	625 mm
Material of worktop	Beech marine ply
Weight	141 kg
Height	950 mm
Material of wheel	Solid rubber
Drawer usable width	500 mm
Push handle	no
Drawer usable depth in G	20
Support cabinet depth	700 mm
Number of drawers	2
Worktop thickness	50 mm
Surface worktop	clear varnished
Number of fixed wheels without parking brake	2
Fixed wheel Ø	100 mm
ComfortClose	no
Worktop length	1500 mm
Support cabinet width	1300 mm
Worktop depth	750 mm
Number of castors without parking brake	2
maximum load capacity, mobile unit	400 kg
Drawer usable width in G	20
Castor Ø	100 mm
can be lowered	yes
Bumper	no
Number of doors	2
Individual drawer release system	One-hand
Plug type, input	F
Nominal voltage	250 V

Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

## Accessories

Lock plate for GridLine Type KO21	914227 KO21
Slide handle for GridLine Type KO12	914226 KO12
Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75