

Garant
Solid carbide special drill DIN 6535 HA, uncoated, Ø DC ±0.003: 3,98 mm

Order data

Order number	121201 3,98
GTIN	4045197715609
Item class	11E

Description
Version:

Spiral flute precision drill for plastics. **Self-centring** with **1-cutter geometry**, achieves **very high alignment accuracy**. **Polished** helical flutes for **optimum chip evacuation**.

Maintains the **tolerance band IT7** from entry Ø through to exit Ø, **due to special point geometry**.

Recommendation:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No.121201 + 129100HB**.

Form **HE**: order with **No.121201 + 129100HE**.

Standard: DIN 6537

Tolerance nominal Ø: ±0.003

Number of cutting edges Z: 1

Semi-Standard: yes

Tolerance nominal Ø: ±0.003

recommended maximum drilling depth L_2 : 30.1 mm

Overall length L: 74 mm

Shank Ø D_s : 4 mm

Feed f in PEEK: 0.15 mm/rev.

Technical description

Flute length L_c	36 mm
Shank tolerance	h6

Number of cutting edges Z	1
Nominal $\varnothing D_c$	3.98 mm
Tolerance nominal \varnothing	± 0.003
Shank $\varnothing D_s$	4 mm
Overall length L	74 mm
Feed f in PEEK	0.15 mm/rev.
Standard	DIN 6537
recommended maximum drilling depth L_2	30.1 mm
Semi-Standard	yes
Coating	uncoated
Tool material	Solid carbide
Drill depth up to	5×D
Point angle	120 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Colour ring	without
Type of product	Jobber drill