Garant

Solid carbide special drill DIN 6535 HA, uncoated, Ø DC ±0.003: 0,97 mm



Order data

Order number	121201 0,97
GTIN	4045197715289
Item class	11E

Description

Version:

Spiral flute precision drill for plastics. Self-centring with 1-cutter geometry, achieves very high alignment accuracy. Polished helical flutes for optimum chip evacuation. **Maintains** the **tolerance band IT7** from entry \emptyset through to exit \emptyset , **due to special point** geometry. **Recommendation:** Flute length $L_c = L_2 + 1.5 \times D_c$. Note: Flute length $L_c = L_2 + 1.5 \times D_c$. Form HB and HE supplied at the same price as HA. Form **HB:** order with **No.121201 + 129100HB**. Form **HE:** order with **No.121201 + 129100HE**. Standard: DIN 6537 Tolerance nominal Ø: ±0.003 Number of cutting edges Z: 1 Semi-Standard: yes Tolerance nominal Ø: ±0.003 recommended maximum drilling depth L₂: 5.6 mm Overall length L: 45 mm Shank Ø D.: 3 mm Feed f in PEEK: 0.1 mm/rev.

Technical description

Shank tolerance	h6
Nominal Ø D _c	0.97 mm

...

...

Number of cutting edges Z	1
Flute length L _c	7 mm
Tolerance nominal Ø	±0.003
Shank Ø D _s	3 mm
Overall length L	45 mm
Feed f in PEEK	0.1 mm/rev.
Standard	DIN 6537
recommended maximum drilling depth L_2	5.6 mm
Semi-Standard	yes
Coating	uncoated
Tool material	Solid carbide
Drill depth up to	5×D
Point angle	120 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Colour ring	without
Type of product	Jobber drill