

SWISS TOOLS

## Cutting head, left-hand, Shank Ø / insert size: 40/11 mm



### Order data

Order number	260311 40/11
GTIN	2050001912282
Item class	29D

### Description

#### Version:

Interchangeable cutting heads for HSK-T and PSC base bodies. Optimum cooling via aligned High Pressure Cooling nozzles.

#### Suitable for :

Boring bar base body **No. 320102; 320103; 320407; 320408.**

Through-coolant: yes

Cutting point / joint: 40 mm

ISO code indexable cutting head: SDQCR/L

suitable indexable insert: DC.. 11T3..

Minimum pre-drill Ø  $D_{min}$ : 50 mm

Centre-line offset: 27 mm

Overall length: 40 mm

### Technical description

ISO code indexable cutting head	SDQCR/L
Cutting point / joint	40 mm
suitable indexable insert	DC.. 11T3..

Insert screw	320624_2
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Insert size	11 mm
Centre-line offset	27 mm
Shank $\varnothing$	40 mm
Overall length	40 mm
Insert assignment	right-hand and neutral
Series	Cutting head
Application type	left-hand
Through-coolant	yes

## Accessories

Torx-screw No. 2 Type 2	320624 2
-------------------------	----------