


Garant**Parting-off insert neutral, HB9140, Groove width w: 8,0mm**

Order data

Order number	273292 8,0
GTIN	4062406085391
Item class	21H

Description

Application:

For parting-off tools No. 273551 – 273558.

Technical description

Corner radius	0.8 mm
Tool material	Carbide
Groove width w	8 mm
Coating	TiAlN ²
Feed f in steel < 900 N/mm ²	0.19 mm/rev.
Main application	M
Cutting conditions	heavily interrupted
Grade	HB9140
Number of changes/inserts	1
Indexable insert profile	neutral
Type of product	Indexable insert for grooving

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	130 m/min	P
Steel < 750 N/mm ²	suitable only under restricted conditions	110 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	90 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	70 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	40 m/min	P
INOX < 900 N/mm ²	suitable	120 m/min	M
INOX > 900 N/mm ²	suitable	100 m/min	M
continuous	suitable		
irregular	suitable only under restricted conditions		
wet maximum	suitable		