

Garant GRIDLINE

Workbench with electric height adjustment, left side cupboard, centre open, right side 4 drawers, Eluplan worktop, dark, 20×20G, Worktop length: 2000/DEmm**Order data**

Order number	921567 2000/DE
GTIN	4062406086558
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Stepless electric drive for height adjustment. Height adjustment by pushbutton. Connecting cable with German Schuko plug. Power supply 250 V / 50 Hz with maximum 340 W. Length of the connecting cable 1.5 m.

Centre part with recessed open housing for ergonomic posture.

Body with door and height-adjustable shelf.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Fitted with:

Door height (left) mm: 525

Number of height-adjustable shelves (left): 1

Drawer front height (right) mm: 75, 100, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When benches are installed in a row, it is essential that additional side plates No. 927220 are fitted.

Technical description

Drawer usable width in G	20
Support cabinet depth	700 mm
Supply voltage	250 V
Height adjustment range	850 - 1050 mm
ComfortClose	no
Worktop thickness	50 mm
Number of drawers	4
Drawer usable depth in G	20
Worktop length	2000 mm
Lifting speed	9 mm/s
Drawer body usable height	525 mm
Stepless height adjustment	yes
maximum lifting force	6000 N
Principle of height adjustment	electrical
Series	Ready-to-go
Worktop depth	750 mm
Drawer usable width	500 mm
Support cabinet width	1900 mm
Weight	174.1 kg
Drawer usable area in G	20×20
Drawer usable depth	500 mm
Electronic locking system can be retrofitted	yes
IP Index of Protection	IP 20

Power supply	Rechargeable battery-powered
Power supply	Mains operated
Plug type, input	F
Nominal voltage	250 V
Design version	Steel hollow section construction
Material thickness	1 mm
Height adjustment workstation	850-1050 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	350 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Drawer Drawer front height 75 mm	927800 75
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 150 mm	927800 150
Lock plate for GridLine Type KO21	914227 KO21