

Solid carbide special drill DIN 6535 HA, uncoated, Ø DC ±0.003: 1,03 mm



Order data

Order number	121201 1,03
GTIN	4045197715449
Item class	11E

Description

Version:

Spiral flute precision drill for plastics. Self-centring with 1-cutter geometry, achieves very high alignment accuracy. Polished helical flutes for optimum chip evacuation. Maintains the tolerance band IT7 from entry \varnothing through to exit \varnothing , due to special point geometry.

Recommendation:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA. Form HB: order with No.121201 + 129100HB. Form HE: order with No.121201 + 129100HE.

Standard: DIN 6537

Tolerance nominal \emptyset : ± 0.003 Number of cutting edges Z: 1

Semi-Standard: yes

Tolerance nominal Ø: ±0.003

recommended maximum drilling depth L₂: 5.5 mm

Overall length L: 45 mm Shank Ø D_s: 3 mm

Feed f in PEEK: 0.1 mm/rev.

Technical description

Number of cutting edges Z	1
Flute length L _c	7 mm

h6
1.03 mm
±0.003
3 mm
45 mm
0.1 mm/rev.
DIN 6537
5.5 mm
yes
uncoated
Solid carbide
5×D
120 degrees
DIN 6535 HA to h6
no
without
Jobber drill