# Garant

Solid carbide special drill DIN 6535 HA, uncoated, Ø DC ±0.003: 8,01 mm



## Order data

Order number	121201 8,01
GTIN	4045197715913
Item class	11E

### Description

#### Version:

Spiral flute precision drill for plastics. Self-centring with 1-cutter geometry, achieves very high alignment accuracy. Polished helical flutes for optimum chip evacuation. **Maintains** the **tolerance band IT7** from entry  $\emptyset$  through to exit  $\emptyset$ , **due to special point** geometry. **Recommendation:** Flute length  $L_c = L_2 + 1.5 \times D_c$ . Note: Flute length  $L_c = L_2 + 1.5 \times D_c$ . Form HB and HE supplied at the same price as HA. Form **HB:** order with **No.121201 + 129100HB**. Form **HE:** order with **No.121201 + 129100HE**. Standard: DIN 6537 Tolerance nominal Ø: ±0.003 Number of cutting edges Z: 1 Semi-Standard: yes Tolerance nominal Ø: ±0.003 recommended maximum drilling depth L<sub>2</sub>: 41 mm Overall length L: 91 mm Shank Ø D.: 8 mm Feed f in PEEK: 0.2 mm/rev.

#### **Technical description**

Flute length $L_c$	53 mm
Nominal Ø D <sub>c</sub>	8.01 mm

129100 HB

Shank grinding Type HB

Number of cutting edges Z	1
Shank tolerance	h6
Tolerance nominal Ø	±0.003
Shank Ø D <sub>s</sub>	8 mm
Overall length L	91 mm
Feed f in PEEK	0.2 mm/rev.
Standard	DIN 6537
recommended maximum drilling depth $L_2$	41 mm
Semi-Standard	yes
Coating	uncoated
Tool material	Solid carbide
Drill depth up to	5×D
Point angle	120 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Colour ring	without
Type of product	Jobber drill
Services	
Shank grinding Type HE	129100 HE