

Garant
SNMG 120408, Grade: HB7020


Order data

Order number	251324 HB7020
GTIN	4045197716484
Item class	21G

Technical description

Feed f	0.25 - 0.8 mm/rev.
Cutting depth a_p	1.5 - 9 mm
Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Chip breaker	SG
Main application	P
Grade	HB7020
Cutting speed v_c main application	100 - 300 m/min
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMG 120408

Number of changes/inserts	8
Type of product	Indexable insert for turning