

Garant**Individual trapezoidal hand tap Second tap, uncoated, Tr: TR10X2****Order data**

Order number	130780 TR10X2
GTIN	4062406087685
Item class	11G

Description**Version:**

3-piece set, **consisting of taper, second, and plug tap.**

- **Taper tap with long pilot pin**
- **Plug tap tolerance H7**

Note:

Tool unsuitable for reversing out.

Thread pitch: 2 mm

Overall length L: 90 mm

Shank Ø D_s: 7 mm

Shank square □: 5.5 mm

Tapping hole Ø: 8.2 mm

Technical description

Overall length L	90 mm
Number of clamping slots	3
Thread pitch	2 mm
Tapping hole Ø	8.2 mm
Shank square □	5.5 mm
Shank Ø D _s	7 mm
Number of cutting edges Z	3
Thread size	10
Coating	uncoated

Thread type	TR
Flank angle	30 degrees
Tool material	HSS E
Standard	Manufacturer's standard
Tolerance class	DIN 103 7H
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap