

Garant
Individual trapezoidal hand tap Second tap, uncoated, Tr: TR10X3

Order data

Order number	130780 TR10X3
GTIN	4062406087692
Item class	11G

Description
Version:

 3-piece set, **consisting of taper, second, and plug tap.**

- **Taper tap with long pilot pin**
- **Plug tap tolerance H7**

Note:
Tool unsuitable for reversing out.

Thread pitch: 3 mm

Overall length L: 100 mm

 Shank Ø D_s: 7 mm

Shank square □: 5.5 mm

Tapping hole Ø: 7.25 mm

Technical description

Tapping hole Ø	7.25 mm
Overall length L	100 mm
Shank Ø D _s	7 mm
Thread pitch	3 mm
Number of cutting edges Z	3
Shank square □	5.5 mm
Number of clamping slots	3
Thread size	10
Coating	uncoated

Thread type	TR
Flank angle	30 degrees
Tool material	HSS E
Standard	Manufacturer's standard
Tolerance class	DIN 103 7H
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap