Garant

Solid carbide special drill DIN 6535 HA, uncoated, Ø DC ±0.003: 5,02 mm



Order data

Order number	121201 5,02
GTIN	4045197715715
Item class	11E

Description

Version:

Spiral flute precision drill for plastics. Self-centring with 1-cutter geometry, achieves very high alignment accuracy. Polished helical flutes for optimum chip evacuation. **Maintains** the **tolerance band IT7** from entry \emptyset through to exit \emptyset , **due to special point** geometry. **Recommendation:** Flute length $L_c = L_2 + 1.5 \times D_c$. Note: Flute length $L_c = L_2 + 1.5 \times D_c$. Form HB and HE supplied at the same price as HA. Form **HB:** order with **No.121201 + 129100HB**. Form **HE:** order with **No.121201 + 129100HE**. Standard: DIN 6537 Tolerance nominal Ø: ±0.003 Number of cutting edges Z: 1 Semi-Standard: yes Tolerance nominal Ø: ±0.003 recommended maximum drilling depth L₂: 36.5 mm Overall length L: 82 mm Shank Ø D_s: 6 mm Feed f in PEEK: 0.15 mm/rev.

Technical description

Nominal Ø D _c	5.02 mm
Number of cutting edges Z	1

Shank tolerance	h6
Flute length L _c	44 mm
Tolerance nominal Ø	±0.003
Shank Ø D _s	6 mm
Overall length L	82 mm
Feed f in PEEK	0.15 mm/rev.
Standard	DIN 6537
recommended maximum drilling depth L_2	36.5 mm
Semi-Standard	yes
Coating	uncoated
Tool material	Solid carbide
Drill depth up to	5×D
Point angle	120 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

Shank grinding Type HB	129100 HB
Shank grinding Type HE	129100 HE