

Garant
Trapezoidal hand tap set, uncoated, Tr: TR10X2

Order data

Order number	130760 TR10X2
GTIN	4062406086985
Item class	11G

Description
Version:

3-piece set, **consisting of taper, second, and plug tap.**

- **Taper tap with long pilot pin**
- **Plug tap tolerance H7**

Note:

Tool unsuitable for reversing out.

Thread pitch: 2 mm

Overall length L: 90 mm

Shank $\varnothing D_s$: 7 mm

Shank square \square : 5.5 mm

Tapping hole \varnothing : 8.2 mm

Technical description

Shank $\varnothing D_s$	7 mm
Overall length L	90 mm
Number of clamping slots	3
Tapping hole \varnothing	8.2 mm
Number of cutting edges Z	3
Thread pitch	2 mm
Shank square \square	5.5 mm

Thread size	10
Coating	uncoated
Thread type	TR
Flank angle	30 °
Tool material	HSS E
Standard	Manufacturer's standard
Tolerance class	DIN 103 7H
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap