

Garant**Individual trapezoidal hand tap Taper tap, uncoated, Tr: TR14X3****Order data**

Order number	130770 TR14X3
GTIN	4062406087616
Item class	11G

Description**Version:**

3-piece set, **consisting of taper, second, and plug tap.**

- **Taper tap with long pilot pin**
- **Plug tap tolerance H7**

Note:

Tool unsuitable for reversing out.

Thread pitch: 3 mm

Overall length L: 130 mm

Shank Ø D_s: 10 mm

Shank square □: 8 mm

Tapping hole Ø: 11.25 mm

Technical description

Thread pitch	3 mm
Tapping hole Ø	11.25 mm
Number of cutting edges Z	3
Overall length L	130 mm
Shank Ø D _s	10 mm
Shank square □	8 mm
Number of clamping slots	3
Thread size	14
Coating	uncoated

Thread type	TR
Flank angle	30 degrees
Tool material	HSS E
Standard	Manufacturer's standard
Tolerance class	DIN 103 7H
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Type of product	Tap