

**Garant****Arbor for screw-in milling cutters with thread, SK 40, Thread M × Length L1:  
M16X150****Order data**

Order number	301309 M16X150
GTIN	4045197718242
Item class	31A

**Description****Version:**

Plain design.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

**Technical description**

Thread M	M16×150
Bore Ø D <sub>1</sub> tolerance IT6	17 mm
Ø D <sub>2</sub>	29 mm
Reach L <sub>1</sub>	150 mm
L <sub>2</sub>	5 mm
Overhang dimension A	169 mm
External Ø D	42.5 mm
Adapter	SK 40
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Threaded copy mill arbor

## Accessories

Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studsealed suitable for steep tapers 40	308660 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
	308740 40

Special pull stud with internal thread suitable for steep tapers 40

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40

308801 40

Pull studForm A suitable for steep tapers 40

308600 40

Pull stud 60°sealed suitable for steep tapers 40

308785 40

Wrench for pull studsISO 7388 suitable for ISO taper size 40

308830 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

308625 40

Pull stud 45°sealed suitable for steep tapers 40

308760 40

Pull stud, 18CrNiMo7Form A suitable for steep tapers 40

308605 40