



Top jaws set, 3 pieces, for chuck type: 210



Order data

Order number	313755 210
GTIN	2050001929785
Item class	33T

Description

Version:

Bevelled for small clamping \emptyset .

Precision milled slots and **precision ground** serrations, **burnished**.

Material:

Quality product made of 16MnCr5.

Suitable for :

Heavy-duty chucks from Schunk, Röhmm and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

suitable for colour code: Schunk heavy-duty chucks and jaws

Length L: 102 mm

Width B: 35 mm

Height H: 40 mm

Hole centre spacing a: 20 mm

Bore spacing b: 25 mm

Slot width D: 14 mm

Technical description

Bore spacing b	25 mm
Length L	102 mm

Slot width D	14 mm
Width B	35 mm
Height H	40 mm
for thread DIN 912	M12
Hole centre spacing a	20 mm
for chuck type	210 mm
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws