

## Garant

### Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 4,8mm



#### Order data

Order number	122690 4,8
GTIN	
Item class	11E

#### Description

##### Version:

**3 guide chamfers** for particularly high accuracy and surface quality at tight hole tolerances.  
**Asymmetrical tip geometry** for **very high metal removal rates**. New generation of **innovative high-performance drills for cast iron** in the HPC field.

##### Advantage:

For HPC high performance drilling in castings. **Outstandingly suitable for bainite cast iron (ADI)**.

##### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122690 + 129100HB** .

Form **HE**: order with **No. 122690 + 129100HE**.

#### Technical description

recommended maximum drilling depth $L_2$	36.8 mm
Tolerance nominal Ø	h7
Shank tolerance	h6
Nominal Ø $D_c$	4.8 mm
Feed $f$ in GJS ADI > 800 N/mm <sup>2</sup>	0.16 mm/rev.
Standard	DIN 6537
Overall length $L$	82 mm
Number of cutting edges $Z$	2

Flute length $L_c$	44 mm
Shank $\varnothing D_s$	6 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	135 °
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	white
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
GG	suitable	110 m/min	K
GGG	suitable	90 m/min	K
GJS, ADI > 800N/mm <sup>2</sup>	suitable	70 m/min	K
wet maximum	suitable		
wet minimum	suitable		

## Services

Shank grinding Type HE	129100 HE
Shank grinding Type HB	129100 HB