

Garant
Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 6,6mm

Order data

Order number	122690 6,6
GTIN	
Item class	11E

Description
Version:

3 guide chamfers for particularly high accuracy and surface quality at tight hole tolerances.
Asymmetrical tip geometry for **very high metal removal rates**. New generation of **innovative high-performance drills for cast iron** in the HPC field.

Advantage:

For HPC high performance drilling in castings. **Outstandingly suitable for bainite cast iron (ADI)**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122690 + 129100HB** .

Form **HE**: order with **No. 122690 + 129100HE**.

Technical description

Feed f in GJS ADI > 800 N/mm ²	0.22 mm/rev.
Number of cutting edges Z	2
Nominal Ø D _c	6.6 mm
Shank Ø D _s	8 mm
Overall length L	91 mm
Tolerance nominal Ø	h7
Flute length L _c	53 mm
recommended maximum drilling depth L ₂	43.1 mm

Standard	DIN 6537
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	135 °
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	white
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
GG	suitable	110 m/min	K
GGG	suitable	90 m/min	K
GJS, ADI > 800N/mm ²	suitable	70 m/min	K
wet maximum	suitable		
wet minimum	suitable		

Services

Shank grinding Type HB	129100 HB
Shank grinding Type HE	129100 HE