

Garant
Solid carbide torus cutter R1 0.2, DLC, Ø DC × L1: 2X16mm

Order data

Order number	206043 2X16
GTIN	4062406089542
Item class	11X

Description
Version:

With **advanced DLC sp² coating**. For the **highest demands regarding performance and precision in aluminium materials**. **Extremely tight tolerances** ensure maximum accuracy. Double-relief ground with 2 chamfers hollow ground.

Recess angle $\alpha = 16^\circ$.

Tolerances:

- **Corner radius: $R_1 = \pm 0.0025$ mm.**
- **Neck Ø: $D_1 = 0 / -0.01$ mm.**

Note:

At greater tool overhang lengths, use a reduced value for a_p !

Values for:

slots milled from solid: $a_p = 0.25 \times D \times a_{p \text{ korr}}$

side milling: $a_p = 0.50 \times D \times a_{p \text{ korr}}$

copying: $a_p = 0.25 \times D \times a_{p \text{ korr}}$

To calculate the feed rate vf please use the actual speed of the machine (the maximum possible speed)!

e.g: $vf = 18000$ [rpm] × fz [mm/Z] × z

Technical description

Overhang length L_1 incl. recess	16 mm
No. of teeth Z	2
Shank	DIN 6535 HA to h5
Feed f_z for copy milling in cast aluminium	0.035 mm
Feed f_z for side milling in cast aluminium	0.035 mm

Overall length L	55 mm
Flute length L_c	2 mm
Corner radius R_1	0.2 mm
Shank $\varnothing D_s$	4 mm
Recess $\varnothing D_1$	1.91 mm
Correction factor $a_{p\ corr}$	0.7
Helix angle	30 degrees
Cutting edge $\varnothing D_c$	2 mm
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Tolerance nominal \varnothing	0 / -0.005
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.5×D for side milling
Through-coolant	no
Colour ring	yellow
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Aluminium	suitable	480 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	400 m/min	N
PMMA acrylic	Suitable	200 m/min	N
PE-HD	Suitable	160 m/min	N
PA 66	Suitable	200 m/min	N

PEEK	Suitable	150 m/min	N
PF 31	Suitable	130 m/min	N
PVDF GF20	suitable	180 m/min	N
POM GF25	Suitable	160 m/min	N
PA 66 GF30	suitable	150 m/min	N
PEEK GF30	suitable	130 m/min	N
PTFE CF25	suitable	160 m/min	N
Cu	suitable	160 m/min	N
CuZn	suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		
Air	suitable		