

**Garant**
**Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 10,1mm**

**Order data**

|              |             |
|--------------|-------------|
| Order number | 122690 10,1 |
| GTIN         |             |
| Item class   | 11E         |

**Description**
**Version:**

**3 guide chamfers** for particularly high accuracy and surface quality at tight hole tolerances.  
**Asymmetrical tip geometry** for **very high metal removal rates**. New generation of **innovative high-performance drills for cast iron** in the HPC field.

**Advantage:**

For HPC high performance drilling in castings. **Outstandingly suitable for bainite cast iron (ADI)**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122690 + 129100HB** .

Form **HE**: order with **No. 122690 + 129100HE**.

**Technical description**

|  |          |
|--|----------|
| Standard                                 | DIN 6537 |
| recommended maximum drilling depth $L_2$ | 55.9 mm  |
| Overall length L                         | 118 mm   |
| Shank Ø $D_s$                            | 12 mm    |
| Tolerance nominal Ø                      | h7       |
| Nominal Ø $D_c$                          | 10.1 mm  |
| Flute length $L_c$                       | 71 mm    |
| Number of cutting edges Z                | 2        |

|   |                   |
|---|-------------------|
| Feed f in GJS ADI > 800 N/mm <sup>2</sup> | 0.29 mm/rev.      |
| Coating                                   | TiAlN             |
| Tool material                             | Solid carbide     |
| Version                                   | 6×D               |
| Point angle                               | 135 °             |
| Shank                                     | DIN 6535 HA to h6 |
| Through-coolant                           | yes, with 25 bar  |
| Machining strategy                        | HPC               |
| Semi-Standard                             | yes               |
| Colour ring                               | white             |
| Type of product                           | Jobber drill      |

## User data

|                                 | Suitability | V <sub>c</sub> | ISO code |
|---------------------------------|-------------|----------------|----------|
| GG                              | suitable    | 110 m/min      | K        |
| GGG                             | suitable    | 90 m/min       | K        |
| GJS, ADI > 800N/mm <sup>2</sup> | suitable    | 70 m/min       | K        |
| wet maximum                     | suitable    |                |          |
| wet minimum                     | suitable    |                |          |

## Services

|                        |           |
|------------------------|-----------|
| Shank grinding Type HB | 129100 HB |
| Shank grinding Type HE | 129100 HE |