


Solid carbide milling cutter, uncoated, Ø e8 DC: 7,5mm

Order data

Order number	202307 7,5
GTIN	4062406093501
Item class	12X

Description
Version:

Dimensions similar to **DIN 6527**.

Note:

Successor product to No. 202240 / 202245.

Technical description

Direction of infeed	horizontal, oblique and vertical
Helix angle	45 degrees
Shank form	HB
Cutting edge Ø D _c	7.5 mm
Feed f _z for slot milling in steel < 750 N/mm ²	0.05 mm
Shank	DIN 6535 HB to h6
Overall length L	63 mm
Shank Ø D _s	8 mm
Flute length L _c	19 mm
Tolerance nominal Ø	e8
Feed f _z for side milling in steel < 750 N/mm ²	0.07 mm
No. of teeth Z	3
Corner chamfer angle	90 degrees

Coating	uncoated
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	170 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	100 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	60 m/min	P
Steel < 900 N/mm ²	suitable	45 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	40 m/min	M
GG(G)	suitable only under restricted conditions	55 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	Suitable		
dry	suitable only under restricted conditions		
Air	Suitable		

