



## Segment jaws set, 3 pieces, Aluminium, for chuck type: 250



### Order data

Order number	313737 250
GTIN	2050001929754
Item class	33T

### Description

**Version:**

**Precision milled** slots and **precision ground** serrations.

**Application:**

All-round low-distortion clamping.

**Suitable for:**

**Heavy-duty chucks** from Schunk, Röhms and other heavy-duty chuck manufacturers.

**Optional extras:**

T-nuts No. 313505 – 313605.

**Note:**

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

Length L	87.5 mm
Width B	180 mm
Hole centre spacing a	40 mm
for chuck type	250 mm
Slot width D	16 mm
Bore spacing b	30 mm
Height H	80 mm

suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws