



## Top jaws set, 3 pieces, for chuck type: 250



### Order data

Order number	313455 250
GTIN	2050001929600
Item class	33T

### Description

#### Version:

**Precision milled** slots and **precision ground** serrations, **burnished**.

Bevelled for small clamping  $\emptyset$ .

#### Material:

Quality product made of 16MnCr5.

#### Suitable for:

**Heavy-duty chucks** from Schunk, Röhm and other heavy-duty chuck manufacturers.

#### Optional extras:

T-nuts No. 313505 – 313605.

#### Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

Bore spacing b	28 mm
Length L	120 mm
Slot width D	21 mm
Width B	50 mm
for chuck type	250 mm
Hole centre spacing a	20 mm
Height H	50 mm

for thread DIN 912

M16

Type of product

Heavy-duty lathe chuck jaws