

**KERN****Pallet scales, Weighing range: 3000kg****Order data**

Order number	919912 3000
GTIN	4045761203204
Item class	96D

**Description****Version:**

Mobile pallet scales. 2 rollers and handle for easy transport of the scales.

Dynamic weighing: Under unstable ambient conditions or when weighing animals, a stable average can be calculated at the touch of a button.

Selectable battery operation. 4 silicone-coated aluminium load cells.

Scale: Steel, powder-coated. Dust-proof and splash-proof IP67.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

With a protective hood, external mains adapter.

**Colour:**

Steel, **powder-coated.**

**Technical description**

Height	110 mm
maximum weighing range	1 - 3000 kg
Depth	1195 mm

Weighing range	3000 kg
Scale divisions	1000 g
Width	840 mm
Number of batteries contained	4
Weight	51 kg
IP Index of Protection	IP 67
Power supply	Battery-powered
Battery type	Mignon, AA
Type of product	Pallet scales