



ROTA-S 2.0 self-centring three-jaw chuck with short taper and scroll stepped jaws, DIN 702-3, Type: 315/8



Order data

Order number	313135 315/8
GTIN	2050001928863
Item class	33U

Description

Version:

- **Maximum concentricity and jaw exchange repeatability.**
- **Long service life with very high precision.**
- **Modular protective sleeve system.**
- **Very short set-up times.**
- **Chuck body case-hardened up to 315 mm Ø.**
- **Large aperture (dimension E!).**
- **Safety peg for maximum operator safety.**
- **Base jaws compatible with chucks of the system "F" and system "Duro".**
- **Flexible clamping of small and large components.**
- **High-precision clamping of very small internal Ø.**

Application:

For spindle noses DIN 55027 with studs and collar nuts. The chuck is always fitted to the spindle nose directly without an intermediate flange.

Standard:

DIN 702-3.

Material:

Entirely made of steel, suitable for high speeds (see table).

Supplied with:

1 safety chuck key and 1 set fastening screws.

1 set scroll stepped jaws.

Optional extras:

For spare and additional jaws see No. 313200 – 313350.

Technical description

Number of studs	4
Size of studs	M16
Aperture E	92 mm
Short taper arbor	8
maximum speed	3400 min ⁻¹
Centring taper Ø B	139.735 mm
Weight	62.6 kg
External Ø A	323 mm
Clamping range with internal hard top jaws	95 - 326 mm
Clamping stroke per jaw S	9.9 mm
Clamping range with external hard top jaws	14 - 333 mm
Type	315
Chuck key hexagon socket K	16 mm
Series	ROTA-S plus
Standard	DIN 702-3
Colour code for accessories	Schunk self-centring chucks and jaws
Type of product	Self-centring chucks

Accessories

Hardened top jaw set, 3 pieces for chuck type 315	313250 315
Base jaw set, 3 pieces,angled serration for chuck type 315	313205 315
Base jaw set, 3 pieces,straight serration for chuck type 315	313207 315

Hardened top jaw set, 3 pieces for chuck type 315	313210 315
Base jaw set, 3 pieces, angled serration for chuck type 315	313200 315