

Garant
CNMG 120408, Type: HU7305


Order data

Order number	250140 HU7305
GTIN	4062406095109
Item class	21G

Description

CNMG 120408 HU7305 Grade: HU7305
 Chip breaker: AM/AG
 Cutting depth a_p : 0.2 - 4 mm
 Feed f : 0.1 - 0.8 mm/rev.
 Cutting speed v_c main application: 400 - 600 m/min

Technical description

Tool material	Carbide
Cutting depth a_p	0.2 - 4 mm
Main application	N
Cutting speed v_c main application	400 - 600 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Grade	HU7305
Feed f	0.1 - 0.8 mm/rev.

Corner radius	0.8 mm
Chip breaker	AM/AG
Cutting conditions	continuous
Coating	uncoated
ISO code indexable insert	CNGG 120408-AM
Number of changes/inserts	4
Type of product	Indexable insert for turning