

3M Scotch-Brite™

Fleece velour-backed abrasive disc GB-DH, Ø 115 mm, Grit equivalent: 50**Order data**

Order number	566902 50
GTIN	50048011644009
Item class	53M

Description**Version:**

Fleece velour-backed abrasive discs with through-stitched backing for hook and loop fastener. With removable centre for more precise positioning and attachment of the disc to the backing pad (**approx. 50 % reduction in vibration level with velour-backed abrasive discs No. 566965**).

Very **aggressive fleece disc** with high edge stability. The integral **ceramic grit (CER)** permits high metal removal rates.

Application:

Ideal for **removal of small weld spatter** and for **coarser cleaning and deburring tasks**. No formation of chatter marks on the surface.

On angle grinders with hook and loop fastener backing pad No. 566960 or 566965.

Note:

See No. **567705ff** onwards for velour-backed abrasive discs for rough abrasion.

Technical description

Grit designation	extra coarse
Version	A coarse super duty

Grit equivalent	50
Colour	blue
Disc Ø	115 mm
Series	GB-DH
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
Manufacturer's designation	GB-DH
maximum circumferential speed	40 m/s
Type of product	Non-woven abrasive

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		

dry

suitable

Accessories

Hook and loop backing pad with Thread M 14 External Ø
115 mm

566960 115

Hook and loop backing pad with Centring and M 14 thread
External Ø 115 mm

566965 115