

**Garant****CCGW 060208 FN, MCD, Cutting edge version: NS**

## Order data

Order number	265904 NS
GTIN	4062406095642
Item class	21L

## Description

**Version:**

**MCD** - mono-crystalline diamond, laser-profiled cutting edges. Honing for synthetic materials (PMMA, POM, acrylics etc.).

**Application:**

For very fine machining for the best finishing surfaces.

**Recommendation:**

For the best results, use the GARANT Master eco system. Alternatively all suitable ISO tool holders and boring bars can be used.

## Technical description

Cutting conditions	continuous
Cutting edge version	NS
Feed f	0.005 - 0.4 mm/rev.
Cutting depth $a_p$	0.01 - 0.2 mm
Grade	MCD

Cutting speed $v_c$ main application	100 - 1400 m/min
Finishing/roughing assignment	Finishing
Tool material	MCD
Coating	uncoated
ISO code indexable insert	CCGW 060208 FN
Number of changes/inserts	1
Product name attribute	MCD
Facility for resharpening	yes
Type of product	Indexable insert for turning