


Garant**CCGW 120408 FN, MCD, Cutting edge version: NK****Order data**

Order number	265936 NK
GTIN	4062406095901
Item class	21L

Description**Version:**

MCD - mono-crystalline diamond, laser-profiled cutting edges. Honing for short-chipping non-ferrous metals.

Application:

For very fine machining for the best finishing surfaces.

Recommendation:

For the best results, use the GARANT Master eco system. Alternatively all suitable ISO tool holders and boring bars can be used.

Technical description

Tool material	MCD
Grade	MCD
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	80 - 1000 m/min
Feed f	0.005 - 0.08 mm/rev.

Cutting depth a_p	0.01 - 0.2 mm
Cutting edge version	NK
Cutting conditions	continuous
Coating	uncoated
ISO code indexable insert	CCGW 120408 FN
Number of changes/inserts	1
Product name attribute	MCD
Facility for resharpening	yes
Type of product	Indexable insert for turning