

Garant**Indexable insert for turning CNMG 12040812, for medium machining****Order data**

Order number	250141 HU7305
GTIN	4062406095826
Item class	21G

Technical description

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Cutting speed v_c main application	400 - 600 m/min
Main application	N
Cutting depth a_p	0.2 - 4 mm
Feed f	0.1 - 0.8 mm/rev.
Type	HU7305
Tool material	Carbide
Chip breaker	AM/AG
Cutting conditions	continuous
Coating	uncoated
ISO code indexable insert	CNMG 12040812

Data sheet

Number of changes/inserts	4
Type of product	Indexable insert for turning