

Garant
HSS core drill N, uncoated, Ø DC h8: 34mm

Order data

| | |
|--------------|---------------|
| Order number | 116620 34 |
| GTIN | 4062406097400 |
| Item class | 11C |

Description
Version:

Strong core. Sturdy jobber drill for better guidance in the hole

Advantage:

Particularly suitable **for drilling out** holes that are out of round. Misaligned holes can be aligned.

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Note:
Please note:

Do not drill the respective tapping hole Ø (see table) less than the stated size.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Technical description

| | |
|--|--------------|
| Morse taper MT size | 4 |
| Flute length L_c | 190 mm |
| Overall length L | 339 mm |
| recommended maximum drilling depth L_2 | 139 mm |
| Feed f in steel $< 750 \text{ N/mm}^2$ | 0.31 mm/rev. |
| Number of cutting edges Z | 3 |
| Nominal Ø D_c | 34 mm |
| Tolerance nominal Ø | h8 |
| Standard | DIN 343 |

| | |
|--|--------------|
| Min. pre-drilling - \varnothing D _{min} | 24 mm |
| Point angle | 120 degrees |
| Shank | Morse taper |
| Coating | uncoated |
| Tool material | HSS |
| Type | N |
| Through-coolant | no |
| Colour ring | without |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 45 m/min | N |
| Steel < 500 N/mm ² | suitable | 40 m/min | P |
| Steel < 750 N/mm ² | suitable | 30 m/min | P |
| Steel < 900 N/mm ² | suitable | 25 m/min | P |
| Steel < 1100 N/mm ² | suitable only under restricted conditions | 10 m/min | P |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | 8 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 12 m/min | M |
| GG(G) | suitable only under restricted conditions | 25 m/min | K |
| wet maximum | suitable | | |