

KERN**Crane scales type HFD, maximum weighing range: 3000kg**

Order data

Order number	479439 3000
GTIN	4045761202764
Item class	47D

Description

Version:

Back-lit LCD display, easily read even from afar. Data hold function for retaining the display value. Sturdy high-resolution crane scales up to 12 tonnes. Character height 30 mm. Battery lasts approx. 30 hours.

Supplied with:

Including remote control with 2 batteries No. 081561 size LR3. Scales incl. battery and mains adapter.

Technical description

Net weight	10 kg
Operating temperature	-10 - 40 °C
Scale divisions	200 g
Overall length	421 mm
Calibration	Price on request
Body width	194 mm

Body height	129 mm
Number of batteries contained	2
Error limit from maximum value	0.2 %
Body depth	145 mm
Article no of the battery / rechargeable battery fitted	081561 LR3
Reading at top of weighing range	1000 g
Reading the average weighing range	500 g
Power supply	Battery-powered
Type of product	Suspended scales / crane scales

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------