

**KERN****Crane scales type HFD, maximum weighing range: 6000kg****Order data**

Order number	479439 6000
GTIN	4045761202771
Item class	47D

**Description****Version:**

Back-lit LCD display, easily read even from afar. Data hold function for retaining the display value. Sturdy high-resolution crane scales up to 12 tonnes. Character height 30 mm. Battery lasts approx. 30 hours.

**Supplied with:**

Including remote control with 2 batteries No. 081561 size LR3. Scales incl. battery and mains adapter.

**Technical description**

Body height	129 mm
Error limit from maximum value	0.2 %
Operating temperature	-10 - 40 °C
Net weight	15 kg
Number of batteries contained	2
Scale divisions	500 g

Calibration	Price on request
Body width	194 mm
Overall length	477 mm
Body depth	145 mm
Article no of the battery / rechargeable battery fitted	081561 LR3
Reading at top of weighing range	2000 g
Reading the average weighing range	1000 g
Power supply	Battery-powered
Type of product	Suspended scales / crane scales

---

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------