



## Platform scales, type EOC, maximum weighing range: 6kg



### Order data

Order number	479606 6
GTIN	4045761192447
Item class	47D

### Description

#### Version:

- Robust stainless steel platform scales can be used as parcel, industrial, and counting scales.
- Dual-range scales with automatic changeover between the ranges (more precise display in the lower half of the weighing range).
- Display unit with numeral height 24 mm can be remote from platform; can be stood or mounted using flexible cable.
- High mobility due to optional battery operation and compact design.
- Provides an optical and acoustic signal to support portioning, metering or sorting within the tolerance range.
- Percentage determination: Enable weighing out to a prescribed value (100%) and determination of deviations from that set value.
- Quantity counting: Easy counting function allows quick counting of large numbers. Reference quantities selectable 5, 10, 25, 50 pieces.
- CAL calibration programme: For setting the accuracy (external calibration weight required for this available on request).

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Supplied with mains adapter, table base including wall bracket, protective hood.

### Technical description

Minimum unit weight	2.5 g
Manufacturer's designation	Type IOC
Calibration	K2
Scale divisions	1 g
Reproducibility	2 g
Net weight	5.2 kg
maximum weighing range	0 - 6 kg
Settling time	2 s
Reading at top of weighing range	2 g
Dimensions of weighing plate	300×300 mm
IP Index of Protection	IP 65
Power supply	Mains-powered
Interface	RS232C interface
Type of product	Platform balance

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/479606-6>