

Garant
Storage trolley, Number of transparent boxes: 63

Order data

Order number	918610 63
GTIN	4062406098124
Item class	91P

Description
NOTE: Colour selection possible
Version:

Frame of hollow steel rectangular section 60×40×2 mm. Sheet metal structure with a black ABS plastic shelf. **4 castors** (2 with parking brakes, **125 mm Ø**) with treadless polyurethane tyres, roller bearing hubs and 2 push handles of Haptoprene® ensure stability and safe handling in the workshop. **Transparent tilt bins** in 4 sizes, made of transparent **ABS plastic** for dust-free storage. Tilt the transparent bins to remove stored goods. Bins can be removed and stacked for assembly purposes.

Application:

For storage / provision of bulk goods and small parts.

Fitted with:

Transparent tilt bins for the front: 18 pcs. 80×63×70 mm;

15 pcs. 100×97×108 mm;

4 pcs. 128×128×133 mm;

3 pcs. 175×140×160 mm

Transparent tilt bins for the rear: 20 pcs. 128×128×133 mm;

3 pcs. 175×140×160 mm

Colour:

RAL 7035 light grey **powder coated**.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 1520 mm

Width: 880 mm

Width without handle: 680 mm

Depth: 600 mm

Wheel Ø: 125 mm

maximum load capacity: 250 kg

Technical description

Number of castors with parking brake	2
Number of castors without parking brake	2
Width without handle	680 mm
maximum load capacity	250 kg
Depth	600 mm
Height	1520 mm
Material of wheels	Treadless polyurethane tyres
Width	880 mm
Weight	77 kg
Wheel Ø	125 mm
Design version	Steel hollow section construction
Material thickness	1.5 mm
Hoffmann perforated panel grid interval	9×9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage trolley

Accessories

Push handle Colour BLUE	920135 BLUE
Push handle Colour BLACK	920135 BLACK