

Marking out and sawing, Number of tools: 8**Order data**

Order number	954987 8
GTIN	2050002005129
Item class	91A

Description**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 954987: 1 pc.
EDDING permanent marker No. 085130 size B: 1 pc.
HOLEX try square No. 452600 size 300×175: 1 pc.
HOLEX protractor No. 453000 size 120×150: 1 pc.
PB carbide scribe No. 458760: 1 pc.
HOLEX precision steel rule No. 461600 size 300: 1 pc.
Tape measure No. 462201 size 2.5: 1 pc.
GARANT hacksaw frame No. 580400: 1 pc.
GARANT hacksaw blades No. 582500 (pack of 10): 1 pc.
Degree of fill of a drawer in units: 10×24
Width: 250 mm
Depth: 600 mm
Width in G: 10
Depth in G: 24

Technical description

Width	250 mm
Width in G	10

Number of tools	8
Depth in G	24
Depth	600 mm
Version	with tool kit
Weight	2.501 kg
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×24
Type of product	Rigid foam inlay

Accessories

Straight carbide scribe with clip and protective cap	458760
Hacksaw blade, single-sided bimetal, progressive	582500
Permanent marker Writing colour B	085130 B
Tape measure with viewing window Band length 2,5 m	462201 2,5
Hacksaw frame with GARANT bimetal blade 18 – 32 TPI progressive	580400
Try square Accuracy class 2 Stock length 300X175 mm	452600 300X175
Protractor with open graduated arc Graduated arc Ø×Stock length 120X150 mm	453000 120X150
Rigid foam inlay for tool sets suitable for rigid foam set 954987	952001 954987
Engineer's precision steel rule stainless, matt finished Length 300 mm	461600 300