

Garant**Sling storage trolley, Type: 12****Order data**

Order number	918601 12
GTIN	4062406098070
Item class	91P

Description**Version:**

Frame and **structure** of rectangular steel hollow section with sheet metal base. Insertion slots in the front and back of the frame (at 50 mm intervals) for fitting size 1000 mm shelves, multi-function rails etc. **Threaded sockets** on the inside of the frame for fitting perforated panels. **4 castors** (2 with parking brakes, Ø 125 mm) with treadless polyurethane tyres, roller bearing hubs and a large push handle with 2-component Haptoprene® cover ensures safe handling.

Application:

Can be equipped with storage shelves, storage container racks, drawing display stands, Multifix rail, cross rail and perforated panels in size 1000.

Supplied with:

1× 918590 size 1700 materials supply trolley,
1× 918603 size 950 cross rails,
6× 918604 size 75 additional hook 75 mm,
6× 918604 size 150 additional hook 150 mm.

Colour:

RAL 7035 light grey **powder coated**.

Technical description

Weight	40 kg
Number of castors with parking brake	2
Width	1100 mm
Suspension interval	50 mm
Material of wheels	Treadless polyurethane tyres
maximum load capacity	200 kg
Wheel Ø	125 mm
Width without handle	1000 mm
Depth	700 mm
Usable width	920 mm
Type	1700/12
Number of castors without parking brake	2
Usable height	1370 mm
Height	1700 mm
Design version	Steel hollow section construction
Height adjustment interval	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Sling storage trolley

Accessories

Push handle Colour BLACK	920135 BLACK
Additional hook Usable length 150 mm	918604 150
Swivel castor Type 1	920137 1
Cross rail suitable for usable width 920 mm	918603 920
Push handle Colour BLUE	920135 BLUE
Swivel castor Type 2	920137 2
Additional hook Usable length 75 mm	918604 75

